


# Tridak® Model 1060 Syringe & Cartridge Filling System

The Tridak® Model 1060 filling system is designed to fill syringes and cartridges, one at a time, quickly and accurately from a material reservoir (sold separately). The system is manually loaded and unloaded, making it ideal for low-volume production or as an alternative to manual filling. It utilizes a Model 830 disposable fluid path valve to make material changeover fast and easy while minimizing cross-contamination. This valve also features adjustable suck-back for accurate, clean cut-off for stringy or tacky materials. The disposable fluid path can be fitted with a variety of nozzles. The system also offers the option to direct all exhaust air from valves outside the production area. The Model 1060 is recommended for use with fluids having a viscosity between 1 - 60,000 cP.

## Features & Benefits:

- Utilizes disposable fluid path valve technology which minimizes cross-contamination, clean-up and downtime during product changeover
- Dispensing valve features adjustable suck-back for a clean dispense of stringy and tacky materials
- An adjustable pneumatic stop assures accurate fills
- Foot switch for hands-free fill cycle activation
- System fills 30-900 mL syringes or cartridges with pre-inserted pistons; tooling nozzles are available for a variety of syringe/ cartridge designs
- Includes a control panel that incorporates:
  - Emergency stop switch
  - Material prime switch
  - Cylinder pressure regulator
- Available with clear or opaque (black) fluid tubing



Model 1060 Syringe & Cartridge Filler

SPECIFICATIONS	
<b>Part Number</b>	<b>T18626</b> (complete)
<b>Input Air Pressure</b>	80 psi (4.1 bar) min to 100 psi (6.9 bar) max
<b>Dimensions (L x W x H)</b>	8.5 in x 12 in x 28.5 in (21.6 cm x 30.48 cm x 72.40 cm)
<b>Viscosity Range</b>	1 - 60,000 cP



© 2018 Dymax Corporation. All rights reserved. All trademarks in this guide, except where noted, are the property of, or used under license by Dymax Corporation, U.S.A.

Please note that most filling and repackaging system applications are unique. Dymax does not warrant the fitness of the product for the intended application. Any warranty applicable to the product, its application and use is strictly limited to that contained in Dymax standard Conditions of Sale published on our website. Dymax recommends that any intended application be evaluated and tested by the user to ensure that desired performance criteria are satisfied. Dymax is willing to assist users in their performance testing and evaluation. Data sheets are available for valve controllers or pressure pots upon request. PB0061 5/21/2018

**Dymax Corporation**  
+1.860.482.1010 | info@dymax.com | [www.dymax.com](http://www.dymax.com)

**Dymax Europe GmbH**  
+49 611.962.7900 | info\_de@dymax.com | [www.dymax.de](http://www.dymax.de)

**Dymax Engineering Adhesives Ireland Ltd.**  
+353 21.237.3016 | info\_ie@dymax.com | [www.dymax.ie](http://www.dymax.ie)

**Dymax Oligomers & Coatings**  
+1.860.626.7006 | info\_oc@dymax.com | [www.dymax-oc.com](http://www.dymax-oc.com)

**Dymax UV Adhesives & Equipment (Shanghai) Co. Ltd.**  
+86.21.37285759 | dymaxasia@dymax.com | [www.dymax.com.cn](http://www.dymax.com.cn)

**Dymax UV Adhesives & Equipment (Shenzhen) Co. Ltd.**  
+86.755.83485759 | dymaxasia@dymax.com | [www.dymax.com.cn](http://www.dymax.com.cn)

**Dymax Asia (H.K.) Limited**  
+852.2460.7038 | dymaxasia@dymax.com | [www.dymax.com.cn](http://www.dymax.com.cn)

**Dymax Asia Pacific Pte. Ltd.**  
+65.6752.2887 | info\_ap@dymax.com | [www.dymax-ap.com](http://www.dymax-ap.com)

**Dymax Korea LLC**  
+82.2.784.3434 | info\_kr@dymax.com | [www.dymax.com/kr](http://www.dymax.com/kr)